




GENERAL COMBUSTION SUPPLIES

774-649	Cleaning Brush Assembly
774-204	Crucible 10/pkg.
502-715	Cotton Thread Fuse, 10 cm, 375/pkg
502-462	Fuse Wire, 10 cm, 375/pkg
621-605-803	Fixed Wire Igniter Assembly, 5/pkg
502-460	Fixed Wire Igniter

OPERATION ACCESSORIES

501-241	Vacuum Grease (Silicone)
633-101-923	AC600 Vessel Holder
621-657	Filter Cartridge, 1 micron
621-605-744	Flush Adapter
762-515	O-Ring Removal Tool
776-978	Glass Scoop
502-051	Tweezers, Curved Fine Point
621-605-517	Vessel Lid Removal Tool
621-605-750	Vessel Tool Kit

OPTIONS

751-350-110	Electronic Balance
621-322	Pellet Press
621-606-160	External Chiller Kit, 120V, 60 Hz (sized for single AC600)
621-606-162	External Chiller Kit, 240V, 50 Hz (sized for single AC600)
621-606-164	External Chiller Kit, 120V, 60 Hz (sized for dual AC600)
621-606-166	External Chiller Kit, 240V, 50 Hz (sized for dual AC600)
633-103-354	Compressed Air Regulator
619-995	Bar Code Scanner USB
621-453-110	Deskjet Printer Kit
621-605-958	AC600 Prep Station
621-605-686	O-Ring Pack for Vessel
621-605-687	O-Ring Pack for Prep Station
621-605-979	Halogen Resistant Combustion Vessel II
621-605-978	Standard Combustion Vessel II

O-RINGS

611-543	Prep Station Nipple Charge
621-605-560	Vessel Cap
621-605-664	Check Valve
621-605-973	Seal Insert Exhaust
772-738	Prep Station Valve Inserts
773-913	Electrode Post
776-562	Ceramic Washer
621-656-001	Water Filter Housing

REFERENCE MATERIALS AND STANDARDS

Current part numbers and values for LECO Reference Materials and Standards (209-296) can be found at <https://www.leco.com/consumables>